



GCOT 10G



GCOT/10G

Description

Dromex® GCOT/10G machine knitted, 10-gauge, cotton blend ambidextrous seamless gloves are designed to keep the users' hands, dry and clean from dust and dirt whilst providing comfort and protection of the hand.

Knit construction stretches for excellent fit, allows circulation of air in the glove and leaves no scratches or fingerprint residue contact on product.

Designed for a multiple range of industrial and household applications, it is ideal for warehousing, general maintenance industries and can be used as a liner glove.

Special Instructions

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The manufacturer has examined under the system for ensuring quality of production by means of monitoring and inspection. The gloves are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. The information contained herein is intended to assist the wearer in the selection of personal protective equipment. Actual conditions of use cannot be directly simulated in a test environment therefore it is the responsibility of the user and not the manufacturer or supplier to determine the gloves suitability for the intended use. All gloves should be thoroughly inspected before use to ensure no damage is present. Immediately discard, should there be a hole on the glove.

Compliance & Conformity

Performs equivalent to the requirements of CE type examinations, EN420 for innocuousness.

Specifications

Style:	Re-useable ambidextrous gloves, winged thumb and knit wristed
Liner:	Cotton blend
Palm:	1.3mm ± 5 %
Back:	1.3mm ± 5 %
Cuff:	Composite knitted wrist with over-locked cuff 1.8mm ± 5 %
Mass:	Part number GCOT ± 37.50 g per pair (10)

Sizes Available

10


Packaging, Storage & Obsolescence

GCOT/10G gloves as sold as 300 pairs per carton for shipping. Store in a cool dry place, away from humidity and out of direct UV and sunlight. Stored correctly, the gloves physical properties will not change for up to 2 – 3 years.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed however, should this not be possible, it is advisable to ease left- and right-hand gloves off, using the gloved hand and remove the gloves without the contaminant contacting the bare hands. The gloves must de-contaminated as indicated below:



GCOT/10G gloves have proven that dry cleaning as well as laundering are suitable cleaning methods.

We recommend that no bleaching or oxidising ingredients or any fabric softeners be used.

Recommended washing temperature is maximum 40°C (104°F) with mild detergents.

The drying process may cause felting on the fabric surface.

Drying temperature should not exceed 60°C (140°F).

There is no remarkable impact on cut resistance during the normal life cycle of a glove however, depending on glove construction, staining and cleaning method, the differences in shrinkage, weight loss, yarn strength and colour may occur.

In order to maximise the glove life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.


Size Available

Code	Size	Palm Length
GCOT/10G	L/10	100mm (±5mm)

** As per the EN420 standard, actual measurement of gloves are determined by the manufacturer, taking into account the behaviour of the glove material, its thickness (such as leather gloves, PVC gloves etc), elasticity and the intended use.*

** Sizing charts only serve as a guide. Sizes and measurements are for reference only. In order to make an informed decision, always try on the gloves as each glove features a unique construction to accommodate a wearer's preferences.*

Measurement Guide



Materials



1. Wing thumb
2. Elasticised wrist
3. Over-locked cuff

Dromex: Unit 1, 1 Blase Road, New Germany, 3620, South Africa
T. +27(31) 713 1960 E. info@dromex.co.za

www.dromex.co.za

Disclaimer

Dromex reserves the right to make changes without further notice to any products herein to improve function, design or reliability and validity. Dromex does not assume any liability arising out of the application or use of any product described herein. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

Latest update: 18/02/2022